

EC326 - DC3  
COVERSHEET

Planned document changes:

Briefly:

No planned changes.

Document changes:

| Date:      | Change:                                | Rev.<br>after change: |
|------------|----------------------------------------|-----------------------|
| 2026-08-20 | Photos updated.                        | B                     |
| 2026-04-22 | Pressure sensor updated. Photos added. | A                     |
| 2025-11-05 | New document.                          | -                     |

Readers note:




Indicates instruction.



Represents Hose.

Dashed lines for overview, mounts  
on other pages/assemblies.



| POS | DESCRIPTION                        | PART    | QTY | COMMENTS        |
|-----|------------------------------------|---------|-----|-----------------|
| 1   | Pressure sensor PT5400             | 7002167 | 3   | Torque: 35Nm    |
| 2   | O-ring 7,65x1,78                   | 710960  | 4   |                 |
| 3   | Directional valve NG4 IQS L 24V DT | 1042190 | 1   |                 |
| 4   | Screw MC6S M5x40 12.9              | 610405  | 3   | Torque: 9,7Nm   |
| 17  | Protective cover EC326 right       | 1081655 | 1   | Part of make up |
| 18  | Protective cover EC326 left        | 1081654 | 1   | Part of make up |
| 19  | Washer NL 10mm                     | 611041  | 4   | Part of make up |
| 20  | Screw M6S M10x25 8,8 FZB           | 610142  | 4   | Part of make up |



Cables



| POS | DESCRIPTION                      | PART    | QTY | COMMENTS |
|-----|----------------------------------|---------|-----|----------|
| 5   | Tiltrotator module DC3 EC326/333 | 8002696 | 1   |          |
| 6   | Washer BRB 5,3x10x1 200 HV FZB   | 611003  | 4   |          |
| 7   | Screw MC6S M5x12 12.9            | 6000077 | 4   |          |
| 8   | Q-Safe connector                 |         |     |          |

POS in order of assembly



Hoses





| POS | DESCRIPTION                  | PART    | QTY | COMMENTS |
|-----|------------------------------|---------|-----|----------|
| 9   | Adapter 45° 402-06-06 (3/8") | 7000090 | 2   |          |
| 10  | Adapter 45° 402-08-08 (1/2") | 7000091 | 2   |          |
| 11  | Hose Tilt 3/8"               | 7002129 | 2   |          |
| 12  | Hose Tilt 1/2"               | 7002130 | 2   |          |
| 13  | Washer GBR12 3/4             | 710706  | 2   |          |
| 14  | Adapter 136-12-12 (3/4")     | 710126  | 2   |          |
| 15  | Hose Feed ECO T              | 7002132 | 1   |          |
| 16  | Hose Feed ECO P              | 7002131 | 1   |          |





Hoses & cables

| POS | DESCRIPTION                      | PART    | QTY | COMMENTS |
|-----|----------------------------------|---------|-----|----------|
| 5   | Tiltrotator module DC3 EC326/333 | 8002696 | 1   |          |
| 8   | Q-Safe connector                 |         |     |          |
| 15  | Hose Feed ECO T                  | 7002132 | 1   |          |
| 16  | Hose Feed ECO P                  | 7002131 | 1   |          |
| ●   | Use cable ties                   |         |     |          |

POS in order of assembly



Hoses & cables



| POS | DESCRIPTION                      | PART    | QTY | COMMENTS |
|-----|----------------------------------|---------|-----|----------|
| 5   | Tiltrotator module DC3 EC326/333 | 8002696 | 1   |          |
| 11  | Hose Tilt 3/8"                   | 7002129 | 2   |          |
| 12  | Hose Tilt 1/2"                   | 7002130 | 2   |          |
| ●   | Use cable ties                   |         |     |          |

Valves

